
- 1. **WALL/KILN SPACING:** 12" [30.5cm] SPACING BETWEEN SIDES OF KILN AND WALLS 4. OR OTHER OBJECTS. 18" [45.7cm] IS RECOMMENDED. LEAVE AT LEAST 18" [45.7cm] BETWEEN TWO KILNS.
- 2. **AMBIENT VENTILATION:** SEE CHART TO RIGHT FOR RATINGS. TO CALCULATE REQUIREMENTS, SEE hotkilns.com/calculate-kiln-room-ventilation.
- 3. **KILN VENTILATION:** L&L VENT-SURE KILN VENT RECOMMENDED FOR SAFETY AND LONGER ELEMENT LIFE. OPTIONAL CONTROL ALLOWS VENT TO BE TURNED ON AND OFF WITH CONTROL.


OTHER INFO: REFER TO INSTALLATION INSTRUCTIONS AND CAUTIONS INSTRUCTIONS FOR OTHER REQUIREMENTS AND SAFETY INFORMATION. REFER TO WIRING DIAGRAM FOR ELECTRICAL HOOKUP INFORMATION.


MAX LOAD WEIGHT: SEE <u>hotkilns.com/load-weight</u>.


6. **WEIGHT OF KILN**: 350 LBS, 159 KG

BTUS/ KILOJOULES PER HOUR NEEDED TO BE VENTED WITH AMBIENT ROOM VENTILATION (THIS IS IN ADDITION TO KILN VENTING):









OPTIONAL FURNITURE KIT: (2) 21" [53.3cm] FULL ROUND SHELVES, (4) HALF ROUND SHELVES, SIX EACH 1/2", 1", 2", 4", 6" & 8" SQUARE POSTS

MADE FROM	DRAWN BY	DATE	SCALE	TITLE		LiKilnes	505 SHARPTOWN RD	REV	SHEET OF	DRAWING NO.
0	DSL	02/01/20	1:12	JD230-JH (2.5" BF	RICK) GENERAL DIMENSIONS	hotkilns.com	PH: (856) 294-0077 FAX: (856) 294-0070	0	3/3	240-000-25-2
		1								

5 4 3 2